



**SKU: PSARSPH** 

#### **Table of Contents**

Features2
Caution2
Schematic View of the Product3
Dimensions4
Product Adjustment4
Adjustable Configurations5
Warranty6
Contact Us6

Before installing and using the product, please carefully read this User Manual to guarantee correct usage and keep it secure for future reference.

# Features

**1.** Combination of Plastic, Metal, and Aluminum Alloy; The entire structure is crafted from high-quality aluminum alloy for a sophis-ticated and minimalist design.

 Accommodates mobile phones or tablets ranging from 4.7 to 12.9 inches.

- 3. The foldable design enables easy storage.
- 4. Features a 360-degree rotatable head for versatile positioning.
- 5. Equipped with an extendable arm for optimal reach.

6. Part of the quick-release series, compatible with various bases for flexible use.

7. Can be securely placed on a table or mounted on a wall.

8. The clamp can securely hold devices with a thickness of 1 to 4 cm.

# Caution


1. The holder is designed to support up to 1 kg. Please do not exceed this weight limit.

2. Usage by children should be under the strict supervision of an adult.


**3.** The user is held responsible for any issues arising from misuse, disassembly, or unauthorized alterations.


**4.** For mounting the product on a wall or glass surface, first remove the 3M adhesive backing from the pin sleeve. Press firmly in place and allow it to set for 24 hours to ensure secure attachment.

#### **Schematic View of the Product**












### Dimensions







## **Product Adjustment**




Step 1: Turn in the direction indicated by the arrow to secure the collet in place.



Step 2: Utilize the large Allen key to adjust the vertical tightness.




Step 3: Employ the medium Allen key for adjusting the vertical tightness.



Step 4: Use the large Allen key to modify the tightness of the base.

### **Adjustable Configurations**

The Rotatable Suction Phone Holder can be adjusted from an upright standing position to a bent configuration, demonstrating the product's flexible arm and pivot points. The product can also be securely attached to a flat vertical surface with its suction base.



# Warranty

Products that you buy directly from our **Powerology** website or shop come with a 24-month warranty.

The 24-month warranty applies to products purchased directly from our **Powerology** website or store. If **Powerology** products are bought from any of our verified retailers, then the product is eligible for only a 12-month warranty. To extend your product's warranty, visit our website **powerology.me/warranty** and fill in your details in the provided form along with an uploaded picture of the product to process your request. Once approved, you will receive a confirmation email of the extended product warranty. Upload the required information within 48 hours of purchase to be eligible for a 24-month warranty period.

For more info, please check: **powerology.me/warranty** 

#### **Contact Us**

If you have any questions about this Privacy Policy, please contact us at: **hey@powerology.me** Website: **powerology.me** Instagram: **powerology\_official** Facebook: **powerology.ME**